

1. DESCRIPTION OF THE PRODUCT

S-100M is a LED curing resin suitable for printing dental model. This material is characterized by its non-toxicity, and high precision in printing. Its mechanical properties, water resistance, and heat resistance enables industrial use. Available in Color; Clear/Gray/Beige

2. Properties of 3D printing resin

Properties	Unit	S-100M	Remark
Color	-	Beige	
Density	g/cm ³ @ 25 °C	1.110 ± 0.02	
Viscosity	cps @ 25 °C	500 ± 30	Brookfield
Solid content	% @ 80 °C * 1h	≥ 98	

3. PROPERTIES OF 3D PRINTING PRODUCT

Properties	Unit	S-100M	Remark
Color	-	Beige	
Shore hardness (D)	-	≥ 90	
Flexural Strength	Мра	≥ 110	ASTM D790
Flexural Modulus	Мра	≥ 2500	ASTM D790
Tensile Strength	Мра	≥ 60	ASTM D638
Tensile Modulus	Мра	≥ 2500	ASTM D638
Elongation	%	≤ 10	ASTM D638
Impact strangth	1 / m²	> 2000	ASTM D256
Impact strength	J/m²	≥ 3000	(Notched)

4. RECOMMENDED CURING CONDITIONS

4-1. INITIAL CURING CONDITIONS

Provision	Unit	Condition	Remark
Light Source	-	UV LED	
Wave Length	nm	405	
Layer Thickness	μ m	100	
UV energy	mJ/cm²	36	UV energy
OV energy	Hij/Cili	30	applied to 1 layer
LED Power	mW/cm²	8	LED Power
LLD FOWEI	ill vv /Cill	O	applied to 1 layer
Exposure time	sec	4.5	
Operation Temp	$^{\circ}$	5 ~ 35	

4-2. Post curing conditions

Provision	Unit	Condition	Remark
Light Source	-	UV LED	
Wave Length	nm	390 - 410	
Operation Temp	$^{\circ}$	5 ~ 35	
	min	5 x 5	Post cure each
Curing time			SIDE, THE FRONT
Curing time			AND BACK OF THE
			PRINTED MODEL
UV energy	mJ/cm²	114000 ~ 120000	UV energy when
ov energy			curing 5min.
LED Power	mW/cm ²	380 ~ 420	

5. How to use

- 1) This product is sensitive to light and should be protected from exposure to sunlight and UV light when stored and used.
- 2) 3D printing resins should be stored and handled in black containers that can prevent exposure to UV light.
- 3) Since it requires a sufficient amount of energy to print the 3D printing parts with this product, it is necessary to periodically check the light intensity of the LED lamp.
- 4) It is recommended to keep the product in the temperature between 15 °C and 25 °C when handling it. If printing with the product at too low or high temperature, it may result in differences in mechanical properties.

6. SHELF LIFE OF PRODUCT

- 12 months from the date of manufacture (stored in cool dark place at 15 ~ 25 °C)
- Storage conditions: 15 ~ 25 °C, shipment to be completed within 30 days of product release

7. NOTE

- The above conditions have been written after review by existing customers and our labs, and are recommended conditions for optimal mechanical properties.
- Even in the same 3D printing, the printing condition may need to be changed depending on the lamp & printing conditions of 3D printers, required mechanical properties and etc.
- Check the line conditions that satisfy the recommended curing conditions before use as the required mechanical properties may not be satisfied depending on the printing conditions even according to the above conditions.

- The information in this document is based on experiments and practical experience. Please note that there are many factors that affect the mechanical properties and quality of the product. Therefore, it is necessary to thoroughly review the product before using it. This document has been written as a reference and we are not legally responsible for this data.
- For more information on the hazards and safety of the product, please check the MSDS (Material Safety Data Sheet). If you have any questions, please contact us.
- This technical data is subject to change without notice and it should be confirmed that this data is recent revision before use.

DATE OF ISSUE 2020, 09, 09.



1. DESCRIPTION OF THE PRODUCT

S-100M is a LED curing resin suitable for printing dental model. This material is characterized by its non-toxicity, and high precision in printing. Its mechanical properties, water resistance, and heat resistance enables industrial use. Available in Color; Clear/Gray/Beige

2. Properties of 3D printing resin

Properties	Unit	S-100M	Remark
Color	-	Gray	
Density	g/cm ³ @ 25 °C	1.110 ± 0.02	
Viscosity	cps @ 25 ℃	500 ± 30	Brookfield
Solid content	% @ 80 °C * 1h	≥ 98	

3. PROPERTIES OF 3D PRINTING PRODUCT

Properties	Unit	S-100M	Remark
Color	-	Gray	
Shore hardness (D)	-	≥ 90	
Flexural Strength	Мра	≥ 110	ASTM D790
Flexural Modulus	Мра	≥ 2500	ASTM D790
Tensile Strength	Мра	≥ 60	ASTM D638
Tensile Modulus	Мра	≥ 2500	ASTM D638
Elongation	%	≤ 10	ASTM D638
Impact strangth	1 / m²	> 2000	ASTM D256
Impact strength	J/m²	≥ 3000	(Notched)

4. RECOMMENDED CURING CONDITIONS

4-1. INITIAL CURING CONDITIONS

Provision	Unit	Condition	Remark
Light Source	-	UV LED	
Wave Length	nm	405	
Layer Thickness	μ m	100	
UV energy	mJ/cm²	46.4	UV energy
OV energy	His/Cili	40.4	applied to 1 layer
LED Power	mW/cm²	8	LED Power
LLD FOWEI	HIVV/CIII		applied to 1 layer
Exposure time	sec	5.8	
Operation Temp	°C	5 ~ 35	

4-2. Post curing conditions

Provision	Unit	Condition	Remark
Light Source	-	UV LED	
Wave Length	nm	390 - 410	
Operation Temp	$^{\circ}$	5 ~ 35	
			Post cure each
Curing time	min	5 x 5	SIDE, THE FRONT
Curing time			AND BACK OF THE
			PRINTED MODEL
UV energy	mJ/cm ²	114000 ~ 120000	UV energy when
ov energy	HID/CHI		curing 5min.
LED Power	mW/cm ²	380 ~ 420	

5. How to use

- 1) This product is sensitive to light and should be protected from exposure to sunlight and UV light when stored and used.
- 2) 3D printing resins should be stored and handled in black containers that can prevent exposure to UV light.
- 3) Since it requires a sufficient amount of energy to print the 3D printing parts with this product, it is necessary to periodically check the light intensity of the LED lamp.
- 4) It is recommended to keep the product in the temperature between 15 °C and 25 °C when handling it. If printing with the product at too low or high temperature, it may result in differences in mechanical properties.

6. SHELF LIFE OF PRODUCT

- 12 months from the date of manufacture (stored in cool dark place at 15 ~ 25 °C)
- Storage conditions: 15 ~ 25 °C, shipment to be completed within 30 days of product release

7. NOTE

- The above conditions have been written after review by existing customers and our labs, and are recommended conditions for optimal mechanical properties.
- Even in the same 3D printing, the printing condition may need to be changed depending on the lamp & printing conditions of 3D printers, required mechanical properties and etc.
- Check the line conditions that satisfy the recommended curing conditions before use as the required mechanical properties may not be satisfied depending on the printing conditions even according to the above conditions.

- The information in this document is based on experiments and practical experience. Please note that there are many factors that affect the mechanical properties and quality of the product. Therefore, it is necessary to thoroughly review the product before using it. This document has been written as a reference and we are not legally responsible for this data.
- For more information on the hazards and safety of the product, please check the MSDS (Material Safety Data Sheet). If you have any questions, please contact us.
- This technical data is subject to change without notice and it should be confirmed that this data is recent revision before use.

DATE OF ISSUE 2020, 09, 09.